


Fabrication Guide



FOME-COR® DISPA® POLAR® SWEDBOARD®
GATOR® SMART-X® SINTRA® LUMEX® G DIBOND®

Quick reference sheet for possible
fabrication methods for 3A products

		Mounting	Repositioning Vinyl	Digital Printing	Screen Printing	Painting	Knife Cutting	Saw Cutting	Routing	Die Cutting/ Punching	Embossing	Forming/Folding	Creasing
\$	FOME-COR FOUNDATION (Acid-Free)	◇ ⁰					◇			◇	◇		
	FOME-COR	◇		◇	◇	◇ ³	◇			◇	◇		◇
	FOME-COR RECOVERY	◇		◇	◇	◇ ³	◇			◇			
	FOME-COR SINGLESTEP (Heat-Activated)	◇					◇			◇	◇		◇
	FOME-COR CANVAS			◇	◇	◇	◇			◇	◇		
	FOME-COR JETMOUNT	◇		◇	◇	◇ ³	◇	◇	◇	◇	◇		
	FOME-COR QUICKSTIK (Self-Adhesive)	◇					◇			◇	◇		◇
	DISPA	◇		◇	◇	◇	◇		◇	◇		◇ ⁷	◇
	NEW! POLAR	◇		◇	◇	◇	◇					◇ ⁷	
\$\$	SINTRA CONSTRUCT	◇ ¹	◇			◇		◇	◇	◇ ⁵		◇	
	SINTRA VERS	◇ ¹	◇	◇	◇	◇	◇ ⁴	◇	◇	◇ ⁵		◇	
	SINTRA	◇ ¹	◇	◇	◇	◇	◇ ⁴	◇	◇	◇ ⁵		◇	
	SINTRA ECLIPSE	◇ ¹	◇	◇	◇	◇	◇ ⁴	◇	◇	◇ ⁵		◇	
	NEW! SINTRA XT	◇ ¹	◇	◇	◇	◇		◇	◇			◇	
	GATORBLANKS	◇				◇ ³	◇	◇	◇				
	NEW! GP APEX	◇	◇	◇	◇	◇ ³	◇	◇	◇	◇ ⁵		◇ ⁷	
	GATORFOAM	◇		◇	◇ ²	◇ ³		◇	◇				
	GATORFOAM SELF-ADHESIVE	◇	◇					◇	◇				
	LUMEX G	◇	◇	◇	◇	◇		◇	◇	◇		◇	
	NEW! SWEDBOARD FIBRE	◇		◇	◇	◇	◇					◇ ⁷	
\$\$\$	DIBOND	◇ ¹	◇	◇	◇	◇		◇	◇	◇ ⁶		◇	

Trialing is recommended to ensure suitability for the proposed fabrication before full-scale commercialization.

- 0 Archival conservation mounting
- 1 Cold mounting techniques only
- 2 Face priming will provide better results
- 3 Do not expose polystyrene foam to solvent-based paints
- 4 1-3mm may be cut with a knife or blade
- 5 May be die cut in gauges up to 5mm or 3/16"
- 6 Punch press die set is required
- 7 V-cut required for folding